



APPROVED 2S. 'STICK' Lithium (LiPo) BATTERY LIST. 2016. v1

List shows years :- 2013 -- 2016.

Only Batteries detailed below (and any archive lists) are approved for EFRA Sanctioned Events.

EUROPEAN FEDERATION RADIO CONTROLLED AUTOMOBILES.

BATTERIES ON THIS HOMOLOGATION LIST HAVE BEEN CERTIFIED FOR COMPLIANCE WITH UN38.3, TESTS T1-T8.

Lithium based (LiPo) batteries detailed below, are approved for various EFRA Electric Classes. Section Rules will detail Classes applicable. EFRA rules do not limit capacity or power output of batteries. Values below are Manufacturers data. -- Packs factory sealed (glue, weld etc). Availability dates for new EFRA compliant Packs are not known at the date of publishing this list. Manufacturers have confirmed March 2016 latest. Battery packs must be able to be disconnected within the Car quickly without the use of tools. Direct soldering is not allowed. Batteries approved from 2011 onwards must comply with the weight range specified under manufacturers data.

It is essential that batteries on this list are charged using a 2S LiPo compatible charger. It is advisable to restrict charge rates to 1C.

It is strictly NOT ALLOWED, to charge 2S LiPo Batteries to give an output voltage exceeding 8.40v. LiPo 'Sack' must be used when charging.








Origin of Supply	Cell Name, Shrink Details	Illustration only	Manufacturer Data.	EFRA measured Specification,	Approval Date
BATTERIES BELOW THIS LEVEL ARE APPROVED BY EFRA FOR 2016 AND ARE ALLOWED AT 2016 EVENTS FROM 01.04.16.					
Associated Electrics	Reedy # 316		Reedy LiPo 2S 7.4v. 37.0 Wh. 65C Wt. 264/286 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 265.6 g.	14.01.16
Associated Electrics	Reedy # 322		Reedy LiPo 2S 7.4v. 40.0 Wh. 70C Wt. 208/226 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 215.0 g.	14.01.16
Associated Electrics	Reedy # 319		Reedy LiPo 2S 7.4v. 29.0 Wh. 70C Wt. 158/172 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 160.8 g.	14.01.16
Freemax Metal Products	Arrowmax # AM 700101		Arrowmax LiPo 2S 7.4v. 37.0 Wh. 55C Wt. 246/266 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 254.7 g.	14.01.16
Freemax Metal Products	Arrowmax # AM 700102		Arrowmax LiPo 2S 7.4v. 44.4 Wh. 65C Wt. 283/307 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 294.8 g.	14.01.16
Freemax Metal Products	Arrowmax # AM 700104		Arrowmax LiPo 2S 7.4v. 57.7 Wh. 55C Wt. 311/337 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 321.5 g.	14.01.16
Freemax Metal Products	Arrowmax # AM 700202		Arrowmax LiPo 2S 7.4v. 37.0 Wh. 55C Wt. 199/215 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 208.4 g.	14.01.16
Freemax Metal Products	Arrowmax # AM 700401		Arrowmax LiPo 2S 7.4v. 20.7 Wh. 55C Wt. 132/143 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 136.5 g.	14.01.16
Intellect Battery	IP # CC2S3500SV1		Intellect LiPo 2S 7.4v. 26.0 Wh. 100C Wt. 139/151 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 142.7 g.	14.01.16
LRP	LRP # 430234		LRP LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 257/279 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 267.5 g.	14.01.16

LRP	LRP # 430232		LRP LiPo 2S 7.4v. 55.5 Wh. 110C Wt. 317/343 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 329.9 g.	14.01.16
LRP	LRP Stock Spec. #'s 430217 (4mm) 430233 (5mm)		LRP LiPo 2S 7.4v. 55.5 Wh. 110C Wt. 317/343 g. 4 or 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 333.8 g.	14.01.16
LRP	LRP # 430235		LRP LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 242/262 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 254.0 g.	14.01.16
LRP	LRP # 430239		LRP LiPo 2S 7.4v. 29.6 Wh. 110C Wt. 179/193 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 186.6 g.	14.01.16
LRP	LRP # 430236		LRP LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 198/214 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 203.5 g.	14.01.16
LRP	LRP Stock Spec. # 430237		LRP LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 202/218 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 205.1 g.	14.01.16
LRP	LRP # 430238		LRP LiPo 2S 7.4v. 22.2 Wh. 110C Wt. 136/148 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 144.3 g.	14.01.16
LRP	LRP # 430245		LRP LiPo 2S 7.4v. 19.2 Wh. 110C Wt. 129/139 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 131.9 g.	14.01.16
LRP	LRP # 430400		LRP LiPo 2S 7.4v. 35.5 Wh. 45C Wt. w/wire 230/250 g.	Sample complies with EFRA dimensions. Sample Wt. 240.3 g.	14.01.16
LRP	LRP # 430401		LRP LiPo 2S 7.4v. 37.0 Wh. 45C Wt. w/wire 238/258 g.	Sample complies with EFRA dimensions. Sample Wt. 247.7 g.	14.01.16
Modern Creations	Team Silverback Spiral R # 64001002SINA		Modern Creations LiPo 2S 7.4v. 47.3 Wh. 100C Wt. 281/305 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 291.9 g.	14.01.16
Modern Creations	Team Silverback Spiral 2 # 6400902SINC		Modern Creations LiPo 2S 7.4v. 47.3 Wh. 90C Wt. 262/284 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 271.1 g.	14.01.16
Modern Creations	Team Silverback Spiral X # 4100902SIN		Modern Creations LiPo 2S 7.4v. 30.3 Wh. 90C Wt. 154/166 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 160.6 g.	14.01.16

Neidhart SA	Orion # ORI 14087		Orion LiPo 2S 7.4v. 42.9 Wh. 110C Wt. 254/276 g. 4mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 265.2 g.	14.01.16
Neidhart SA	Orion # ORI 14068		Orion LiPo 2S 7.4v. 33.3 Wh. 100C Wt. 197/213 g. 5mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 205.7 g.	14.01.16
Neidhart SA	Orion # ORI 14083		Orion LiPo 2S 7.4v. 37.0 Wh. 110C Wt. 204/221 g. 4mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 217.8 g.	14.01.16
Neidhart SA	Orion # ORI 14081		Orion LiPo 2S 7.4v. 23.7 Wh. 110C Wt. 125/135 g. 4mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 131.5 g.	14.01.16
Neidhart SA	Orion # ORI 14082		Orion LiPo 2S 7.4v. 28.1 Wh. 110C Wt. 146/158 g. 4mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 147.4 g.	14.01.16
Nosram	Nosram X-treme Race # 999527		Nosram LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 257/279 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 266.7 g.	14.01.16
Nosram	Nosram X-treme Race # 999525		Nosram LiPo 2S 7.4v. 55.5 Wh. 110C Wt. 317/343 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 333.9 g.	14.01.16
Nosram	Nosram Stock Spec. # 's 999524 (4mm) 999526 (5mm)		Nosram LiPo 2S 7.4v. 55.5 Wh. 110C Wt. 317/343 g. 4 or 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 331.1 g.	14.01.16
Nosram	Nosram X-treme Race # 999528		Nosram LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 242/262 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 256.4 g.	14.01.16
Nosram	Nosram X-treme Race # 999532		Nosram LiPo 2S 7.4v. 29.6 Wh. 110C Wt. 179/193 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 187.5 g.	14.01.16
Nosram	Nosram X-treme Race # 999529		Nosram LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 198/214 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 206.2 g.	14.01.16
Nosram	Nosram X-treme Race Stock Spec. # 999530		Nosram LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 202/218 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 206.1 g.	14.01.16
Nosram	Nosram X-treme Race # 999531		Nosram LiPo 2S 7.4v. 22.2 Wh. 110C Wt. 136/148 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 145.3 g.	14.01.16



Nosram	Nosram X-treme Race # 999538		Nosram LiPo 2S 7.4v. 19.2 Wh. 110C Wt. 129/139 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 132.9 g.	14.01.16
RC Concept	Omega # 50C5180100T		RC Concept LiPo 2S 7.4v. 59.2 Wh. 100C Wt. 303/329 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 310.5 g.	14.01.16
RC Concept	Omega # 50C5145000T		RC Concept LiPo 2S 7.4v. 33.3 Wh. 100C Wt. 194/210 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 202.2 g.	14.01.16
RC Concept	Omega # 50C5133400T		RC Concept LiPo 2S 7.4v. 24.4 Wh. 100C Wt. w/wire 144/156 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 150.1 g.	14.01.16
Revell GmbH	TrakPower # TKPC0370		TrakPower LiPo 2S 7.4v. 30.0 Wh. 50C Wt. 226/244 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 237.5 g.	14.01.16
Revell GmbH	TrakPower # TKPC0716		TrakPower LiPo 2S 7.4v. 40.0 Wh. 100C Wt. 278/302 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 281.1 g.	14.01.16
Revell GmbH	TrakPower # TKPC0375		TrakPower LiPo 2S 7.4v. 40.0 Wh. 50C Wt. 254/276 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 263.8 g.	14.01.16
Revell GmbH	TrakPower # TKPC0721		TrakPower LiPo 2S 7.4v. 47.0 Wh. 100C Wt. 312/338 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 330.6 g.	14.01.16
Revell GmbH	TrakPower # TKPC0365		TrakPower LiPo 2S 7.4v. 30.0 Wh. 50C Wt. 192/208 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 202.3 g.	14.01.16
Revell GmbH	TrakPower # TKPC0710		TrakPower LiPo 2S 7.4v. 31.0 Wh. 100C Wt. 192/208 g. 5 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 202.1 g.	14.01.16
Revell GmbH	TrakPower # TKPC0707		TrakPower LiPo 2S 7.4v. 22.0 Wh. 100C Wt. 140/152 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 143.9 g.	14.01.16
Shenzhen Grepow	GensAce # B50C50002S1P H/Case 47		GensAce LiPo 2S 7.4v. 37.0 Wh. 50C Wt. 286/310 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 286.5 g.	14.01.16
Shenzhen Grepow	GensAce # B65C53002S1P H/Case 47		GensAce LiPo 2S 7.4v. 39.2 Wh. 65C Wt. 294/318 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 299.9 g.	14.01.16


Shenzhen Grepow	GensAce # B70C60002S1P H/Case 47		GensAce LiPo 2S 7.4v. 44.4 Wh. 70C Wt. 307/333 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 309.4 g.	14.01.16
Shenzhen Grepow	GensAce # B50C65002S1P H/Case 47		GensAce LiPo 2S 7.4v. 48.1 Wh. 50C Wt. 303/329 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 308.4 g.	14.01.16
Shenzhen Grepow	GensAce # B60C42002S2P H/Case 29		GensAce LiPo 2S 7.4v. 31.1 Wh. 60C Wt. 206/224 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 212.9 g.	14.01.16
Shenzhen Grepow	GensAce # B60C46002S2P H/Case 29		GensAce LiPo 2S 7.4v. 34.0 Wh. 60C Wt. 197/213 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 201.7 g.	14.01.16
Shenzhen Grepow	GensAce # B50C50002S2P H/Case 29A		GensAce LiPo 2S 7.4v. 37.0 Wh. 50C Wt. 202/218 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 211.0 g.	14.01.16
Shenzhen Grepow	GensAce # B60C32002S1P H/Case 58		GensAce LiPo 2S 7.4v. 23.7 Wh. 60C Wt. 144/156 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 146.9 g.	14.01.16
Vapex Technology	VP Racing # VP96412		Vapex LiPo 2S 7.4v. 45.0 Wh. 80C Wt. 289/313 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 301.8 g.	14.01.16
Vapex Technology	VP Racing # VP96429		Vapex LiPo 2S 7.4v. 58.0 Wh. 70C Wt. 296/320 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 307.4 g.	14.01.16
Vapex Technology	VP Racing # VP96436		Vapex LiPo 2S 7.4v. 39.5 Wh. 70C Wt. 200/216 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 209.7 g.	14.01.16
Yokomo	Racing Performer # RPB-60L		Yokomo LiPo 2S 7.4v. 44.4 Wh. 100C Wt. 298/322 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 311.0 g.	14.01.16
Yokomo	Racing Performer # RPB-50S		Yokomo LiPo 2S 7.4v. 37.0 Wh. 100C Wt. 206/224 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 215.5 g.	14.01.16
Yokomo	Racing Performer # RPB-39E2K		Yokomo LiPo 2S 7.4v. 28.8 Wh. 100C Wt. 154/166 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 159.7 g.	14.01.16
French ONPower	ONPower # 75074141		ONPower LiPo 2S 7.4v. 55.5 Wh. 75C Wt. 307/333 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 318.5 g.	14.01.16

French ONPower	ONPower # 46074142		ONPower LiPo 2S 7.4v. 34.0 Wh. 90C Wt. 204/220 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 209.5 g.	14.01.16
Italtrading	EZ-Power # EZP4600/2		Ital LiPo 2S 7.4v. 34.0 Wh. 70C Wt. 202/218 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 209.3 g.	14.01.16
MaxTime	MTB # MTB213		Maxtime LiPo 2S 7.4v. 34.0 Wh. 100C Wt. 207/224 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 216.4 g.	14.01.16
Muchmore Racing	Impact # MLI-MP6200FD2		Muchmore LiPo 2S 7.4v. 45.9 Wh. 110C Wt. 298/322 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 311.3 g.	14.01.16
Muchmore Racing	Impact # MLI-ST5000FD2		Muchmore LiPo 2S 7.4v. 37.0 Wh. 110C Wt. 206/224 g. 4 mm. Tubes.	Sample complies with EFRA dimensions. Sample Wt. 214.4 g.	14.01.16
ProTek RC	ProTek RC # PTKLPH4300 2S100S		ProTek LiPo 2S 7.4v. 31.8 Wh. 100C Wt. 202/218 g. 4 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 205.7 g.	14.01.16
Tianco	ORCA Infinite # OBHV63G2		Tianco LiPo 2S 7.4v. 46.6 Wh. 100C Wt. 271/293 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 281.1 g.	14.01.16

BATTERIES BELOW THIS LEVEL WERE APPROVED BY EFRA FOR 2015 AND ARE ALLOWED AT ALL 2016 EVENTS.

Intellect Battery	IP # CC2S6000SV1		Intellect LiPo 2S 7.4v. 44.0 Wh. 100C Wt. 271/293 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 283.7 g.	08.01.15
Intellect Battery	IP # CC2S7800SV1		Intellect LiPo 2S 7.4v. 58.0 Wh. 100C Wt. 312/338 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 323.8 g.	08.01.15
Intellect Battery	IP # BG2S5000SV1		Intellect LiPo 2S 7.4v. 37.0 Wh. 100C Wt. 202/218 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 211.7 g.	08.01.15
LRP	LRP # 430221		LRP LiPo 2S 7.4v. 40.7 Wh. 110C Wt. 275/297 g.	Sample complies with EFRA dimensions. Sample Wt. 288.3 g.	08.01.15
LRP	LRP # 430223		LRP LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 261/283 g.	Sample complies with EFRA dimensions. Sample Wt. 275.6 g.	08.01.15
LRP	LRP # 430222		LRP LiPo 2S 7.4v. 42.9 Wh. 110C Wt. 276/300 g.	Sample complies with EFRA dimensions. Sample Wt. 288.6 g.	08.01.15

LRP	LRP # 430220		LRP LiPo 2S 7.4v. 51.8 Wh. 110C Wt. 313/339 g.	Sample complies with EFRA dimensions. Sample Wt. 328.3 g.	08.01.15
LRP	LRP # 430228		LRP LiPo 2S 7.4v. 31.8 Wh. 110C Wt. 204/220 g.	Sample complies with EFRA dimensions. Sample Wt. 211.2 g.	08.01.15
LRP	LRP # 430227		LRP LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 204/220 g.	Sample complies with EFRA dimensions. Sample Wt. 210.9 g.	08.01.15
LRP	LRP # 430229		LRP LiPo 2S 7.4v. 21.5 Wh. 110C Wt. 136/148 g.	Sample complies with EFRA dimensions. Sample Wt. 142.5 g.	08.01.15
LRP	LRP # 430218		LRP LiPo 2S 7.4v. 19.2 Wh. 110C Wt. 129/139 g.	Sample complies with EFRA dimensions. Sample Wt. 134.0 g.	08.01.15
Modern Creations	Team Silverback SpiralX # 7800902SINA		Modern Creations LiPo 2S 7.4v. 57.7 Wh. 90C Wt. 300/326 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 313.5 g.	08.01.15
Modern Creations	Team Silverback SpiralX # 5200902SIN-96		Modern Creations LiPo 2S 7.4v. 38.5 Wh. 90C Wt. 211/229 g.	Sample complies with EFRA dimensions. Sample Wt. 220.4 g.	08.01.15
Muchmore Racing	Impact # MLI-IH6000FD2		Muchmore LiPo 2S 7.4v. 44.4 Wh. 90C Wt. 272/294 g.	Sample complies with EFRA dimensions. Sample Wt. 280.1 g.	08.01.15
Muchmore Racing	Impact # MLI-IH7200FD2		Muchmore LiPo 2S 7.4v. 53.3 Wh. 100C Wt. 307/333 g.	Sample complies with EFRA dimensions. Sample Wt. 325.9 g.	08.01.15
Muchmore Racing	Impact # MLI-ST4500FD2		Muchmore LiPo 2S 7.4v. 33.3 Wh. 90C Wt. 197/213 g.	Sample complies with EFRA dimensions. Sample Wt. 199.8 g.	08.01.15
Nosram	Nosram X-treme Race # 999515		Nosram LiPo 2S 7.4v. 40.7 Wh. 110C Wt. 275/297 g.	Sample complies with EFRA dimensions. Sample Wt. 285.3 g.	08.01.15
Nosram	Nosram X-treme Race # 999517		Nosram LiPo 2S 7.4v. 41.4 Wh. 110C Wt. 261/283 g.	Sample complies with EFRA dimensions. Sample Wt. 275.1 g.	08.01.15
Nosram	Nosram X-treme Race # 999516		Nosram LiPo 2S 7.4v. 42.9 Wh. 110C Wt. 276/300 g.	Sample complies with EFRA dimensions. Sample Wt. 291.0 g.	08.01.15

Nosram	Nosram X-treme Race # 999514		Nosram LiPo 2S 7.4v. 51.8 Wh. 110C Wt. 313/339 g.	Sample complies with EFRA dimensions. Sample Wt. 326.3 g.	08.01.15
Nosram	Nosram X-treme Race # 999522		Nosram LiPo 2S 7.4v. 31.8 Wh. 110C Wt. 204/220 g.	Sample complies with EFRA dimensions. Sample Wt. 215.8 g.	08.01.15
Nosram	Nosram X-treme Race # 999521		Nosram LiPo 2S 7.4v. 33.3 Wh. 110C Wt. 204/220 g.	Sample complies with EFRA dimensions. Sample Wt. 212.7 g.	08.01.15
Nosram	Nosram X-treme Race # 999523		Nosram LiPo 2S 7.4v. 21.5 Wh. 110C Wt. 136/148 g.	Sample complies with EFRA dimensions. Sample Wt. 142.7 g.	08.01.15
Nosram	Nosram X-treme Race # 999512		Nosram LiPo 2S 7.4v. 19.2 Wh. 110C Wt. 129/139 g.	Sample complies with EFRA dimensions. Sample Wt. 134.9 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR55002S50B		Optipower LiPo 2S 7.4v. 40.7 Wh. 50C Wt. 288/312 g.	Sample complies with EFRA dimensions. Sample Wt. 299.6 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR55002S50FL		Optipower LiPo 2S 7.4v. 40.7 Wh. 50C Wt. w/wire 298/322 g.	Sample complies with EFRA dimensions. Sample Wt. 310.3 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR65002S50B		Optipower LiPo 2S 7.4v. 48.1 Wh. 50C Wt. 295/319 g.	Sample complies with EFRA dimensions. Sample Wt. 307.1 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR65002S50FL		Optipower LiPo 2S 7.4v. 48.1 Wh. 50C Wt. w/wire 289/313 g.	Sample complies with EFRA dimensions. Sample Wt. 300.8 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR70002S50B		Optipower LiPo 2S 7.4v. 51.8 Wh. 50C Wt. 300/326 g.	Sample complies with EFRA dimensions. Sample Wt. 313.1 g.	08.01.15
Process Measurement & Analysis	Optipower # OPR70002S50FL		Optipower LiPo 2S 7.4v. 51.8 Wh. 50C Wt. w/wire 302/328 g.	Sample complies with EFRA dimensions. Sample Wt. 314.5 g.	08.01.15
Pro Models Corally	Corally # 48275		Pro Models LiPo 2S 7.4v. 42.9 Wh. 100C Wt. 288/312 g.	Sample complies with EFRA dimensions. Sample Wt. 299.0 g.	08.01.15
Pro Models Corally	Corally # 48276		Prp Models LiPo 2S 7.4v. 50.3 Wh. 100C Wt. 307/333 g.	Sample complies with EFRA dimensions. Sample Wt. 319.6 g.	08.01.15

Pro Models Corally	Corally # 48277		Pro Models LiPo 2S 7.4v. 55.5 Wh. 100C Wt. 298/322 g.	Sample complies with EFRA dimensions. Sample Wt. 309.1 g.	08.01.15
Pro Models Corally	Corally # 48280		Pro Models LiPo 2S 7.4v. 33.3 Wh. 100C Wt. 198/214 g.	Sample complies with EFRA dimensions. Sample Wt. 205.6 g.	08.01.15
Pro Models Corally	Corally # 48262		Pro Models LiPo 2S 7.4v. 35.5 Wh. 90C Wt. 193/209 g.	Sample complies with EFRA dimensions. Sample Wt. 200.7 g.	08.01.15
ProTek RC	ProTek RC # PTK 5104-15		ProTek LiPo 2S 7.4v. 39.2 Wh. 100C Wt. 271/293 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 283.9 g.	08.01.15
ProTek RC	ProTek RC # PTK 5107-15		ProTek LiPo 2S 7.4v. 47.4 Wh. 100C Wt. 312/338 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 324.9 g.	08.01.15
ProTek RC	ProTek RC # PTK 5102-15		ProTek LiPo 2S 7.4v. 31.5 Wh. 100C Wt. 202/218 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 209.3 g.	08.01.15
ProTek RC	ProTek RC # PTK 5100-15		ProTek LiPo 2S 7.4v. 20.7 Wh. 100C Wt. 141/153 g.	Sample complies with EFRA dimensions. Sample Wt. 147.9 g.	08.01.15
Ruddog Dist.	Vampire # VR-1027		Vampire LiPo 2S 7.4v. 47.4 Wh. 100C Wt. 307/333 g.	Sample complies with EFRA dimensions. Sample Wt. 317.9 g.	08.01.15
Ruddog Dist.	Vampire # VR-1026		Vampire LiPo 2S 7.4v. 55.5 Wh. 80C Wt. 317/343 g.	Sample complies with EFRA dimensions. Sample Wt. 327.0 g.	08.01.15
Ruddog Dist.	Vampire # VR-1028		Vampire LiPo 2S 7.4v. 34.0 Wh. 80C Wt. 211/229 g.	Sample complies with EFRA dimensions. Sample Wt. 217.4 g.	08.01.15
Shenzhen Grepow	GensAce # B70C72002S1 P H/Case10		GensAce LiPo 2S 7.4v. 53.3 Wh. 70C Wt. 302/327 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 314.1 g.	08.01.15
Tianco	ORCA Infinite # OBHV62N8		Tianco LiPo 2S 7.4v. 45.9 Wh. 100C Wt. 271/293 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 282.6 g.	08.01.15
Tianco	ORCA Infinite # OBHV75I9		Tianco LiPo 2S 7.4v. 55.5 Wh. 100C Wt. 312/338 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 325.8 g.	08.01.15

Tianco	ORCA Infinite # OBHV48F7		Tianco LiPo 2S 7.4v. 35.5 Wh. 100C Wt. 202/218 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 214.1 g.	08.01.15
Yokomo	Racing Performer # RBP-58R		Yokomo LiPo 2S 7.4v. 42.9 Wh. 100C Wt. 263/285 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 274.0 g.	08.01.15
Yokomo	Racing Performer # RBP-48S		Yokomo LiPo 2S 7.4v. 35.5 Wh. 100C Wt. 202/218 g. 5 mm. Tubes	Sample complies with EFRA dimensions. Sample Wt. 213.0 g.	08.01.15
Yokomo	Racing Performer # RBP-35E2		Yokomo LiPo 2S 7.4v. 25.9 Wh. 100C Wt. 141/153 g.	Sample complies with EFRA dimensions. Sample Wt. 144.9 g.	08.01.15
MaxTime	MTB # MTB315		Maxtime LiPo 2S 7.4v. 48.1 Wh. 100C Wt. 303/329 g.	Sample complies with EFRA dimensions. Sample Wt. 316.1 g.	08.01.15
Associated Electrics	Reedy # 602		Reedy LiPo 2S 7.4v. 31.0 Wh. 65C Wt. 200/216 g.	Approved for 2013. Label design updated for 2015. Specification not changed.	08.01.15
BATTERIES BELOW THIS LEVEL WERE APPROVED BY EFRA FOR 2014 AND ARE ALLOWED AT ALL 2016 EVENTS.					
Associated Electrics	Reedy # 313		Reedy LiPo 2S 7.4v. 52.0 Wh. 65C Wt. 305/331 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 315.6 g.	05.01.14
CS- Electronic	CS Professional # C211032		CS LiPo 2S 7.4v. 56.3 Wh. 90C Wt. 321/347 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 328.9 g.	05.01.14
CS- Electronic	CS Professional # C211026		CS LiPo 2S 7.4v. 35.5 Wh. 90C Wt. 209/227 g.	Sample complies with EFRA dimensions. Wt. 215.9 g.	05.01.14
Hacker Motor	Hacker Top Fuel # 77200277		Hacker LiPo 2S 7.4v. 50.3 Wh. 90C Wt. 300/325 g.	Sample complies with EFRA dimensions. Wt. 300.6 g.	05.01.14
Hacker Motor	Hacker Top Fuel # 74500277		Hacker LiPo 2S 7.4v. 31.1 Wh. 90C Wt. 199/215 g.	Sample complies with EFRA dimensions. Wt. 204.7 g.	05.01.14
Hobbico RC	TrakPower # TKPC0616		TrakPower LiPo 2S 7.4v. 42.0 Wh. 90C Wt. 283/306 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 294.8 g.	05.01.14
Hobbico RC	TrakPower # TKPC0621		TrakPower LiPo 2S 7.4v. 54.0 Wh. 90C Wt. 312/338 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 336.0 g.	05.01.14

Hobbico RC	TrakPower # TKPC0610		TrakPower LiPo 2S 7.4v. 34.0 Wh. 90C Wt. 211/229 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 220.2 g.	05.01.14
Hobbico RC	TrakPower # TKPC0607		TrakPower LiPo 2S 7.4v. 24.0 Wh. 90C Wt. 144/156 g.	Sample complies with EFRA dimensions. Wt. 153.2 g.	05.01.14
Intellect Battery	IP # CC2S6000V9		Intellect LiPo 2S 7.4v. 44.0 Wh. 90C Wt. 283/307 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 295.6 g.	05.01.14
Intellect Battery	IP # CC2S7600V9		Intellect LiPo 2S 7.4v. 56.0 Wh. 90C Wt. 321/348 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 336.5 g.	05.01.14
Intellect Battery	IP # BG2S4800V9		Intellect LiPo 2S 7.4v. 36.0 Wh. 90C Wt. 211/229 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 219.8 g.	05.01.14
VTEC LRP	VTEC # 430211		LRP LiPo 2S 7.4v. 44.4 Wh. 55C Wt. 282/306 g.	Sample complies with EFRA dimensions. Wt. 294.3 g.	05.01.14
VTEC LRP	VTEC # 430210		LRP LiPo 2S 7.4v. 55.5 Wh. 55C Wt. 318/345 g.	Sample complies with EFRA dimensions. Wt. 334.2 g.	05.01.14
VTEC LRP	VTEC # 430214		LRP LiPo 2S 7.4v. 34.8 Wh. 55C Wt. 213/231 g.	Sample complies with EFRA dimensions. Wt. 221.8 g.	05.01.14
Modern Creations	Team Silverback Elite # 5300502SINA		Team Silverback LiPo 2S 7.4v. 39.22 Wh. 50C Wt. 245/265 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 254.9 g.	05.01.14
Modern Creations	Team Silverback SpiralX # 6300902SINA		Team Silverback LiPo 2S 7.4v. 46.62 Wh. 90C Wt. 283/307 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 294.2 g.	05.01.14
Modern Creations	Team Silverback Spiral # 7200802SINA		Team Silverback LiPo 2S 7.4v. 53.28 Wh. 80C Wt. 297/322 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 312.0 g.	05.01.14
Muchmore Racing	Muchmore Impact # MLI- IH6000SP		Muchmore LiPo 2S 7.4v. 44.4 Wh. 80C Wt. 278/302 g.	Sample complies with EFRA dimensions. Wt. 288.5 g.	05.01.14
Muchmore Racing	Muchmore Impact # MLI- ST4600FD		Muchmore LiPo 2S 7.4v. 34.0 Wh. 80C Wt. 211/229 g.	Sample complies with EFRA dimensions. Wt. 221.9 g.	05.01.14

Neidhart SA	ORION Carbon Pro # ORI 14061		Orion LiPo 2S 7.4v. 42.9 Wh. 100C Wt. 296/320 g.	Sample complies with EFRA dimensions. Wt. 307.7 g.	05.01.14
Neidhart SA	ORION Carbon Pro # ORI 14062		Orion LiPo 2S 7.4v. 50.3 Wh. 100C Wt. 301/327 g.	Sample complies with EFRA dimensions. Wt. 312.4 g.	05.01.14
Neidhart SA	ORION Carbon Pro # ORI 14060		Orion LiPo 2S 7.4v. 50.3 Wh. 100C Wt. w/wire 305/331 g.	Sample complies with EFRA dimensions. Wt. w/wires 316.1 g.	05.01.14
Neidhart SA	ORION Carbon Pro # ORI 14066		Orion LiPo 2S 7.4v. 31.1 Wh. 100C Wt. 198/214 g.	Sample complies with EFRA dimensions. Wt. 203.4 g.	05.01.14
VTEC Nosram	Nosram X-treme Race # 999508		Nosram LiPo 2S 7.4v. 44.4 Wh. 55C Wt. 282/306 g.	Sample complies with EFRA dimensions. Wt. 294.3 g.	05.01.14
VTEC Nosram	Nosram X-treme Race # 999507		Nosram LiPo 2S 7.4v. 55.5 Wh. 55C Wt. 318/345 g.	Sample complies with EFRA dimensions. Wt. 334.2 g.	05.01.14
VTEC Nosram	Nosram X-treme Race # 999511		Nosram LiPo 2S 7.4v. 34.8 Wh. 55C Wt. 213/231 g.	Sample complies with EFRA dimensions. Wt. 221.8 g.	05.01.14
Pro Models BVBA	Corally # 48257		Corally LiPo 2S 7.4v. 44.4 Wh. 90C Wt. 286/310 g.	Sample complies with EFRA dimensions. Wt. 299.4 g.	05.01.14
Pro Models BVBA	Corally # 48256		Corally LiPo 2S 7.4v. 51.8 Wh. 90C Wt. 307/333 g.	Sample complies with EFRA dimensions. Wt. 319.9 g.	05.01.14
Pro Models BVBA	Corally # 48255		Corally LiPo 2S 7.4v. 59.2 Wh. 90C Wt. 312/338 g.	Sample complies with EFRA dimensions. Wt. 318.6 g.	05.01.14
ProTek RC	ProTek RC # PTK 5104-14		ProTek LiPo 2S 7.4v. 42.9 Wh. 100C Wt. 283/307 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 295.0 g.	05.01.14
ProTek RC	ProTek RC # PTK 5107-14		ProTek LiPo 2S 7.4v. 54.7 Wh. 100C Wt. 321/348 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 336.8 g.	05.01.14
ProTek RC	ProTek RC # PTK 5102-14		ProTek LiPo 2S 7.4v. 34.7 Wh. 100C Wt. 211/229 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 221.5 g.	05.01.14

ProTek RC	ProTek RC # PTK 5100-14		ProTek LiPo 2S 7.4v. 23.6 Wh. 100C Wt. 144/156 g.	Sample complies with EFRA dimensions. Wt. 153.4 g.	05.01.14
Tianco	ORCA Infinite # OB6290G6		Orca LiPo 2S 7.4v. 45.9 Wh. 90C Wt. 283/307 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 295.7 g.	05.01.14
Tianco	ORCA Infinite # OB7590GT		Orca LiPo 2S 7.4v. 55.5 Wh. 90C Wt. 322/348 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 339.5 g.	05.01.14
Tianco	ORCA Infinite # OB4890P5		Orca LiPo 2S 7.4v. 35.5 Wh. 90C Wt. 211/229 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 221.0 g.	05.01.14
Trinity Revtech Epic	RevTech FormulaX # REV2021-5		Revtech LiPo 2S 7.4v. 52.9 Wh. 100C Wt. 298/322 g. 5mm. Tubes	Sample complies with EFRA dimensions. Wt. 310.2 g.	05.01.14
Xcite RC	Xcite Energy XXL # 56600103		Xcite LiPo 2S 7.4v. 42.9 Wh. 80C Wt. 283/307 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Wt. 296.0 g.	05.01.14
Xcite RC	Xcite Energy XXL # 56600102		Xcite LiPo 2S 7.4v. 54.8 Wh. 80C Wt. 322/348 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Wt. 337.4 g.	05.01.14
Xcite RC	Xcite Energy XXL # 56600105		Xcite LiPo 2S 7.4v. 34.0 Wh. 80C Wt. 211/229 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Wt. 221.5 g.	05.01.14
Fullymax	Fullymax # FB6400 80C 7.4 WB		Fullymax LiPo 2S 7.4v. 47.3 Wh. 80C Wt. 307/333 g.	Sample complies with EFRA dimensions. Wt. 315.4 g.	05.01.14
Fullymax	Fullymax # FB7500 45C 7.4 WB		Fullymax LiPo 2S 7.4v. 55.5 Wh. 45C Wt. 314/340 g.	Sample complies with EFRA dimensions. Wt. 322.1 g.	05.01.14
Graupner	GM V-MAXX # 99031		GM LiPo 2S 7.4v. 56.2 Wh. 100C Wt. 322/348 g.	Sample complies with EFRA dimensions. Wt. 328.6 g.	05.01.14
Moore Speed	Moore-Speed # MS-B7408		M/Speed LiPo 2S 7.4v. 45.9 Wh. 80C Wt. 295/319 g.	Sample complies with EFRA dimensions. Wt. 310.4 g.	05.01.14
nVision	nVision # NVO 1120		nVision LiPo 2S 7.4v. 42.9 Wh. 100C Wt. 302/327 g.	Sample complies with EFRA dimensions. Wt. 313.2 g.	05.01.14

nVision	nVision # NVO 1118		nVision LiPo 2S 7.4v. 42.9 Wh. 100C Wt. w/wire 305/331 g.	Sample complies with EFRA dimensions. Wt. w/wires 317.6 g.	05.01.14
nVision	nVision # NVO 1121		nVision LiPo 2S 7.4v. 50.3 Wh. 100C Wt. 308/334 g.	Sample complies with EFRA dimensions. Wt. 319.1 g.	05.01.14
nVision	nVision # NVO 1119		nVision LiPo 2S 7.4v. 50.3 Wh. 100C Wt. w/wire 311/337 g.	Sample complies with EFRA dimensions. Wt. w/wires 322.0 g.	05.01.14
nVision	nVision # NVO 1125		nVision LiPo 2S 7.4v. 31.1 Wh. 100C Wt. 197/213 g.	Sample complies with EFRA dimensions. Wt. 202.9 g.	05.01.14
RC Industries Int.	Pro Amps # PA6060002S		Pro Amps LiPo 2S 7.4v. 44.4 Wh. 60C Wt. 292/316 g.	Sample complies with EFRA dimensions. Wt. 303.2 g.	05.01.14
RC Industries Int.	Pro Amps # PA6042002S2 P		Pro Amps LiPo 2S 7.4v. 31.1 Wh. 60C Wt. 185/201 g.	Sample complies with EFRA dimensions. Wt. 194.8 g.	05.01.14
Shanghai Dualsky	Track & Field # 31085		Dualsky LiPo 2S 7.4v. 51.8 Wh. 80C Wt. 301/327 g. 5mm. Tubes.	Sample complies with EFRA dimensions. Wt. 326.4 g.	05.01.14
Shanghai Dualsky	Track & Field # 31097		Dualsky LiPo 2S 7.4v. 34.0 Wh. 75C Wt. 202/218 g.	Sample complies with EFRA dimensions. Wt. 207.7 g.	05.01.14
Shenzhen Acepow Electronics	Gens ace # B50C50002S1 PH/Case10		Acepow LiPo 2S 7.4v. 37.0 Wh. 50C Wt. 291/316 g.	Sample complies with EFRA dimensions. Wt. 292.3 g.	05.01.14
Shenzhen Acepow Electronics	Gens ace # B65C53002S1 PH/Case10		Acepow LiPo 2S 7.4v. 39.2 Wh. 65C Wt. 301/326 g.	Sample complies with EFRA dimensions. Wt. 301.9 g.	05.01.14
Shenzhen Acepow Electronics	Gens ace # B45C58002S2 PH/Case10		Acepow LiPo 2S 7.4v. 42.9 Wh. 45C Wt. 304/329 g.	Sample complies with EFRA dimensions. Wt. 304.7 g.	05.01.14
BATTERIES BELOW THIS LEVEL WERE APPROVED BY EFRA FOR 2013 AND ARE ALLOWED AT ALL 2016 EVENTS.					
Arrowind Hobby	Black Magic # BM A35 5002A		Arrowind Hobby LiPo 2S 7.4v. 37.0 Wh. 35C Wt. 268/290 g. Also in Carbon/F finish.	Complies with EFRA. specified dimensions. Wt. 278.2 g.	02.01.13
Arrowind Hobby	Black Magic # BM A99 6602D		Arrowind Hobby LiPo 2S 7.4v. 48.84 Wh. 99C Wt. 296/320 g. Also in Carbon/F finish.	Complies with EFRA. specified dimensions. Wt. 307.5 g.	02.01.13

Associated Electrics	Reedy # 309		Reedy LiPo 2S 7.4v. 57.0 Wh. 65C Wt. 305/331 g.	Complies with EFRA. specified dimensions. Wt. 315.2 g.	02.01.13
Associated Electrics	Reedy # 602		Reedy LiPo 2S 7.4v. 31.0 Wh. 65C Wt. 200/216 g.	Complies with EFRA. specified dimensions. Wt. 206.5 g.	02.01.13
Graupner	GM V-MAXX # 99027		GM LiPo 2S 7.4v. 47.36 Wh. 70C. Wt. 280/304 g.	Complies with EFRA. specified dimensions. Wt. 293.7 g.	02.01.13
Graupner	GM V-MAXX # 99024		GM LiPo 2S 7.4v. 53.28 Wh. 70C. Wt. 307/333 g.	Complies with EFRA. specified dimensions. Wt. 321.6 g.	02.01.13
Graupner	GM V-MAXX # 99020		GM LiPo 2S 7.4v. 33.3 Wh. 70C. Wt. 206/224 g.	Complies with EFRA. specified dimensions. Wt. 214.8 g.	02.01.13
Hacker Motor	Hacker Top Fuel # 7400277		Hacker LiPo 2S 7.4v. 29.6 Wh. 90C. Wt. 205/223 g.	Complies with EFRA. specified dimensions. Wt. 211.9 g.	02.01.13
Intellect Battery	IP # CC2S6000V8		Intellect LiPo 2S 7.4v. 44.0 Wh. 80C Wt. 286/310 g. 5mm. Tubes	Complies with EFRA. specified dimensions. Wt. 298.9 g.	02.01.13
Intellect Battery	IP # CC2S7200V8		Intellect LiPo 2S 7.4v. 53.0 Wh. 80C Wt. 312/338 g. 5mm. Tubes	Complies with EFRA. specified dimensions. Wt. 326.1 g.	02.01.13
Intellect Battery	IP # BG2S4600V8		Intellect LiPo 2S 7.4v. 34.0 Wh. 80C Wt. 206/223 g.	Complies with EFRA. specified dimensions. Wt. 215.6 g.	02.01.13
VTEC	VTEC # 430205		LRP LiPo 2S 7.4v. 38.5 Wh. 40C Wt. 242/262 g.	Complies with EFRA. specified dimensions. Has chassis location. Wt. 253.1 g.	02.01.13
VTEC	VTEC # 430206		LRP LiPo 2S 7.4v. 42.2 Wh. 40C Wt. 283/307 g.	Complies with EFRA. specified dimensions. Wt. 296.3 g.	02.01.13
VTEC	VTEC # 430201		LRP LiPo 2S 7.4v. 51.8 Wh. 55C Wt. 303/328 g.	Complies with EFRA. specified dimensions. Wt. 317.1 g.	02.01.13
VTEC	VTEC Big Mama. # 430200		LRP LiPo 2S 7.4v. 53.5 Wh. 50C Wt. 311/337 g.	Complies with EFRA. specified dimensions. Wt. 325.7 g.	02.01.13

VTEC	VTEC # 430204		LRP LiPo 2S 7.4v. 33.3 Wh. 55C Wt. 207/224 g.	Complies with EFRA. specified dimensions. Wt. 217.2 g.	02.01.13
Modern Creations	Team Silverback Venus # 7300752SIN		Team Silverback LiPo 2S 7.4v. 54.02 Wh. 75C Wt. 302/327 g.	Complies with EFRA. specified dimensions. Wt. 312.5 g.	02.01.13
Modern Creations	Team Silverback Venus # 4700752SIN-96		Team Silverback LiPo 2S 7.4v. 34.78 Wh. 75C Wt. 202/219 g.	Complies with EFRA. specified dimensions. Wt. 206.9 g.	02.01.13
Team ORION	ORION Carbon Pro # ORI 14056		Orion LiPo 2S 7.4v. 59.2 Wh. 90C Wt. 301/326 g.	Complies with EFRA. specified dimensions. Wt. 309.0 g.	02.01.13
Team ORION	ORION Carbon Pro # ORI 14057		Orion LiPo 2S 7.4v. 59.2 Wh. 90C Wt. w/wire 306/331 g.	Complies with EFRA. specified dimensions. Wt. w/wire 312.1 g.	02.01.13
Team ORION	ORION Carbon Pro # ORI 14055		Orion LiPo 2S 7.4v. 29.6 Wh. 90C Wt. 206/223 g.	Complies with EFRA. specified dimensions. Wt. 210.0 g.	02.01.13
VTEC	Nosram X-treme Race # 999505		Nosram LiPo 2S 7.4v. 38.5 Wh. 40C Wt. 241/261 g.	Complies with EFRA. specified dimensions. Has chassis location. Wt. 252.1 g.	02.01.13
VTEC	Nosram X-treme Race # 999506		Nosram LiPo 2S 7.4v. 42.2 Wh. 40C Wt. 284/308 g.	Complies with EFRA. specified dimensions. Wt. 297.7 g.	02.01.13
VTEC	Nosram X-treme Race # 999501		Nosram LiPo 2S 7.4v. 51.8 Wh. 55C Wt. 303/328 g.	Complies with EFRA. specified dimensions. Wt. 317.9 g.	02.01.13
VTEC	Nosram X-treme Race Big Mama # 999500		Nosram LiPo 2S 7.4v. 53.5 Wh. 50C Wt. 311/337 g.	Complies with EFRA. specified dimensions. Wt. 328.8 g.	02.01.13
VTEC	Nosram X-treme Race # 999504		Nosram LiPo 2S 7.4v. 33.3 Wh. 55C Wt. 207/224 g.	Complies with EFRA. specified dimensions. Wt. 216.6 g.	02.01.13
Tianco	ORCA Infinite # OB608015		Tianco LiPo 2S 7.4v. 44.4 Wh. 80C Wt. 286/310 g. 5mm. Tubes	Complies with EFRA. specified dimensions. Wt. 298.0 g.	02.01.13
Tianco	ORCA Infinite # OB7080G5		Tianco LiPo 2S 7.4v. 51.8 Wh. 80C Wt. 312/338 g. 5mm. Tubes	Complies with EFRA. specified dimensions. Wt. 328.2 g.	02.01.13

Tianco	ORCA Infinite # OB45480P4		Tianco LiPo 2S 7.4v. 33.3 Wh. 80C Wt. 206/223 g.	Complies with EFRA. specified dimensions. Wt. 214.8 g.	02.01.13
Vampire Racing	Vampire # VR-1022		Vampire LiPo 2S 7.4v. 31.0 Wh. 30C Wt. 230/249 g.	Complies with EFRA. specified dimensions. Has chassis locations Wt. 238.0 g.	02.01.13
Vampire Racing	Vampire # VR-1021		Vampire LiPo 2S 7.4v. 39.0 Wh. 30C Wt. 274/297 g.	Complies with EFRA. specified dimensions. Wt. 286.9 g.	02.01.13
Vampire Racing	Vampire # VR-1020		Vampire LiPo 2S 7.4v. 53.0 Wh. 70C Wt. 302/327 g.	Complies with EFRA. specified dimensions. Wt. 315.3 g.	02.01.13
Vapex Technology	VP Racing # VP95057		Vapex LiPo 2S 7.4v. 52.5 Wh. 65C Wt. 300/325 g.	Complies with EFRA. specified dimensions. Wt. 312.9 g.	02.01.13
Vapex Technology	VP Racing # VP95071		Vapex LiPo 2S 7.4v. 35.0 Wh. 65C Wt. 195/211 g.	Complies with EFRA. specified dimensions. Wt. 204.4 g.	02.01.13
Acorn Innovations	Acorn Mad Series # 1111446		Acorn LiPo 2S 7.4v. 32.6 Wh. 70C Wt. 184/199 g.	Complies with EFRA. specified dimensions. Wt. 191.9 g.	02.01.13
Corally RC BV	Corally # 48254		Corally LiPo 2S 7.4v. 51.8 Wh. 45C Wt. 302/327 g.	Complies with EFRA. specified dimensions. Wt. 315.1 g.	02.01.13
Fullymax	Fullymax # FB6000 70C JC		Fullymax LiPo 2S 7.4v. 44.4 Wh. 70C Wt. 307/332 g.	Complies with EFRA. specified dimensions. Wt. 319.5 g.	02.01.13
Fullymax	Fullymax # FB7000 45C JC		Fullymax LiPo 2S 7.4v. 51.8 Wh. 45C Wt. 307/332 g.	Complies with EFRA. specified dimensions. Wt. 325.1 g.	02.01.13
Fullymax	Fullymax # FB4600 45C JC		Fullymax LiPo 2S 7.4v. 30.1 Wh. 45C Wt. 207/224 g.	Complies with EFRA. specified dimensions. Wt. 219.6 g.	02.01.13
HUECO Handels	H-Speed # HSP-0009		H-Speed LiPo 2S 7.4v. 48.0 Wh. 80C Wt. 296/320 g.	Complies with EFRA. specified dimensions. Wt. 309.9 g.	02.01.13
HUECO Handels	H-Speed # HSP-0008		H-Speed LiPo 2S 7.4v. 33.0 Wh. 60C Wt. 195/211 g.	Complies with EFRA. specified dimensions. Wt. 206.0 g.	02.01.13

Italtrading	EZ-Power # EZP7200/2		Ital LiPo 2S 7.4v. 53.0 Wh. 70C Wt. 307/332 g.	Complies with EFRA. specified dimensions. Wt. 325.9 g.	02.01.13
nVision	nVision # NVO 1113		nVision LiPo 2S 7.4v. 59.2 Wh. 90C Wt. 301/326 g.	Complies with EFRA. specified dimensions. Wt. 308.0 g.	02.01.13
nVision	nVision # NVO 1114		nVision LiPo 2S 7.4v. 59.2 Wh. 90C Wt. w/wire 301/326 g.	Complies with EFRA. specified dimensions. Wt. w/wire 308.0 g.	02.01.13
nVision	nVision # NVO 1112		nVision LiPo 2S 7.4v. 29.6 Wh. 90C Wt. 206/223 g.	Complies with EFRA. specified dimensions. Wt. 211.5 g.	02.01.13
Shanghai Dualsky	Track & Field # 33843		Dualsky LiPo 2S 7.4v. 47.0 Wh. 75C Wt. 293/317 g.	Complies with EFRA. specified dimensions. Wt. 307.4 g.	02.01.13
Shenzhen Acepow Electronics	Gens ace # B5070002S2P HC10		Acepow LiPo 2S 7.4v. 51.8 Wh. 50C Wt. 296/320 g.	Complies with EFRA. specified dimensions. Wt. 304.1 g.	02.01.13

Paul Worsley, (EFRA Battery Homologation Officer). Updated - 15.01.16. (Eighteen Pages).